


Non-return valves

Both sides fitted with inner threads (in inch)

Opening pressure 1 bar (standard design)



Series	Pressure*	d1	SW1	SW4	l1	i1	kg/100 approx.	Order No.
L 6	PB 250	G 1/8 A	19	19	50.5	8	10.4	0 6 70 25 20 00**
L 6	PB 250	G 1/4 A	19	19	55	12	11.7	0 6 70 26 20 00
L 10	PB 250	G 3/8 A	24	27	68.5	12	21.0	0 6 70 27 20 00
L 15	PB 250	G 1/2 A	32	36	74	14	35.5	0 6 70 28 20 00
L 18	PB 160	G 3/4 A	41	46	84	16	80.7	0 6 70 29 20 00
L 22	PB 160	G 1 A	46	50	96.5	18	89.2	0 6 70 30 20 00
L 28	PB 100	G 1 1/4 A	60	60	110	20	189.0	0 6 70 31 20 00
L 35	PB 100	G 1 1/2 A	65	70	119	22	237.6	0 6 70 32 20 00

* Test pressure PP = 1.5 x table value

** Sample product code, see: RHD1/8